

Measuring tools set, Number of tools: 7



Order data

Order number	952070 7
GTIN	2050002004061
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 952070: 1 pc.
 GARANT digital caliper No. 412680 size 150: 1 pc.
 GARANT external micrometer No. 420402 size 0-25: 1 pc.
 GARANT bevel edge square No. 450010 size 150×100: 1 pc.
 HOLEX carbide scribe No. 458800 size HM: 1 pc.
 GARANT steel rule No. 461770 size 300: 1 pc.
 GARANT tape measure No. 462210 size 3: 1 pc.
 WIHA plastic folding rule No. 466200 size 2: 1 pc.

Technical description

Depth in G	16
Width	200 mm
Weight	1.65 kg
Number of tools	7
Depth	400 mm

Width in G	8
Version	with measurement tool
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8×16
Type of product	Rigid foam inlay

Accessories

Digital caliper IP54 with data output Measuring range 150 mm	412680 150
Steel rule, stainless Length 300 mm	461770 300
Bevel edge square, flat version stainless, accuracy class 00 Stock length 150X100 mm	450010 150X100
Tape measure with viewing window Band length 3 m	462210 3
Plastic folding rule Length 2 m	466200 2
Rigid foam inlay for tool sets suitable for rigid foam set 952070	952001 952070
External micrometer Measuring range 0-25 mm	420402 0-25
Straight carbide scriber Type	458800