



## Double open ended spanner set, Number of tools: 12



### Order data

Order number	952535 12
GTIN	4062406152642
Item class	91A

### Description

#### Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

#### Supplied with:

Rigid foam inlay, empty No. 952001 size 952535: 1 pc.

HOLEX double open ended spanner set No. 610960 size 12 (6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×23; 24×26; 27×32; 30×34): 1 pc.

### Technical description

Depth in G	24
Width in G	10
Width	250 mm
Depth	600 mm
Number of tools	12
Version	with spanners (ring spanners and open-ended spanners)
Weight	2.808 kg
Rigid foam quality LD45, thickness	30 mm

Degree of fill of a drawer in units	10x24
Type of product	Rigid foam inlay

## Accessories

Double open ended spanner Jaw widths 12X13 mm	610950 12X13
Rigid foam inlay for tool sets suitable for rigid foam set 952535	952001 952535
Double open ended spanner Jaw widths 24X26 mm	610950 24X26
Double open ended spanner Jaw widths 20X22 mm	610950 20X22
Double open ended spanner Jaw widths 14X15 mm	610950 14X15
Double open ended spanner Jaw widths 18X19 mm	610950 18X19
Double open ended spanner Jaw widths 8X9 mm	610950 8X9
Double open ended spanner Jaw widths 30X34 mm	610950 30X34
Double open ended spanner Jaw widths 21X23 mm	610950 21X23
Double open ended spanner Jaw widths 10X11 mm	610950 10X11
Double open ended spanner Jaw widths 27X32 mm	610950 27X32
Double open ended spanner Jaw widths 16X17 mm	610950 16X17
Double open ended spanner Jaw widths 6X7 mm	610950 6X7
Double open ended spanner set Number of keys 12	610960 12