



Straight die grinder Cordless, Type: GGS18V23



Order data

Order number	077263 GGS18V23
GTIN	3165140945721
Item class	03C

Description

Version:

Cordless straight die grinder with sturdy and heavy-duty brushless motor.

- **with long neck and performance equal to that of a main cable model (equivalent to 1000 Watt).**

Electronic Motor Protection (EMP) protects the motor against overloading and ensures a long working life.

- **Compact design and low weight for comfortable handling.**
- **Bosch Electronic Cell Protection (ECP): protects the battery against overheating and deep discharge.**

Supplied with:

Without battery, without charger. Supplied with 6 mm collet, 2x AF 13 and AF 19 tightening wrenches, L-BOXX.

Technical description

suitable battery - supplier / battery type / voltage	Bosch 18 V
electronic speed pre-selection	no
maximum collet \varnothing	8 mm
Battery voltage	18 V
maximum vibration to EN	3.5 m/s ²
Weight	1.8 kg
Speed range	22000 min ⁻¹

Manufacturer's designation	GG518 V-23 LC
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	0
Power supply	Rechargeable battery-powered
Packaging	Modular case (L-Boxx)
Type of product	Straight die grinder

Accessories

Li-ion battery Battery type, battery voltage B18 V	073853 B18
Battery charger Type GAL18160C	073866 GAL18160C
click & go starter set 18 V / 6.3 AhEneRacer Manufacturer's designation B1863	P07341 B1863
Li-ion battery Battery type, battery voltage B18 V	073851 B18
Li-ion battery Battery type, battery voltage B18 V	073854 B18
Battery charger Type 1880CV	073866 1880CV