



## Cordless angle grinder GWS, Type: 18-125V-LI



### Order data

Order number	077120 18-125V-LI
GTIN	
Item class	03C

### Description

#### Version:

**Extremely powerful 18 V cordless angle grinder** in compact design:

- **Very long runtime thanks to robust 4-pole motor with protection against overload, overheating and deep discharge.**
- **3-stage speed pre-selection and personalised tool configuration using the Bosch my tools app.**

#### Supplied with:

**Without batteries** and without charger. Including L-BOXX, anti-twist safety guard, mounting flange, clamping nut, additional handle, 1/1 L-BOXX inlay for device and charger, two-pin wrench.

#### Note:

See No. 073854 and No. 073866 for suitable spare batteries and chargers.

### Technical description

Battery voltage	18 V
maximum disc Ø	125 mm
Weight	2.3 kg
Manufacturer's designation	GWS 18-125 V-LI
Overload protection	yes

Kick-back stop	no
Soft start	no
maximum vibration to EN	6 m/s <sup>2</sup>
maximum cutting depth	34 mm
maximum speed	10000 min <sup>-1</sup>
suitable battery - supplier / battery type / voltage	Bosch 18 V
Restart block	yes
Dead man's circuit	no
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Packaging	Modular case (L-Boxx)
Power supply	Rechargeable battery-powered
Type of product	Angle grinder

## Accessories

Li-ion battery Battery type, battery voltage B18 V	073853 B18
Battery charger Type 1880CV	073866 1880CV
Battery starter setProCore Battery type, battery voltage C18 V	073867 C18
Battery starter setProCore Battery type, battery voltage C18 V	073865 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073857 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073856 C18
Li-ion battery Battery type, battery voltage B18 V	073851 B18
Battery charger Type GAL18160C	073866 GAL18160C
Li-ion batteryProCore Battery type, battery voltage C18 V	073858 C18
Li-ion battery Battery type, battery voltage B18 V	073854 B18
Battery starter setProCore Battery type, battery voltage C18 V	073863 C18

