



TMSERROR, Type: GBH18V-26F



Order data

Order number	075515 GBH18V-26F
GTIN	3165140956451
Item class	03B

Description

Version:

18-V cordless hammer drill with SDS-plus tool mounting and brushless motor.

- **Overload clutch to protect both user and machine.**
- **Reversible.**
- **Extremely sturdy: Electronic Motor Protection switches off the motor if it is overloaded. Fully operational even after a drop test from 2 m on to concrete.**

Cordless hammer drill ideal for everyday use.

- **Full control thanks to KickBack Control and Electronic Precision Control.**
- **Clean working made possible through combination with the optional GDE 18V-16 dust extraction system.**

Advantage:

Brushless motor.

Supplied with:

Supplied with 2 pcs. 18 V / 8.0 Ah **ProCore battery**, charger, 13 mm quick-change drill chuck, depth stop, additional handle, L-Boxx 136.

Note:

Suitable carbide hammer drills can be found from No. 787000. Suitable spare batteries and chargers can be found under No. 073851 – 073866.

Technical description

maximum twist drill size Ø in wood	30 mm
Packaging	Modular case (L-Boxx)
Impact energy	2.6 J
maximum twist drill size Ø in concrete	26 mm
Tool arbor shape	SDS-Plus
suitable battery - supplier / battery type / voltage	Bosch 18 V
Weight	3.6 kg
Battery voltage	18 V
maximum vibration to EN	13 m/s ²
Manufacturer's designation	GBH 18V-26 F
maximum twist drill size Ø in steel	13 mm
maximum hammer rate	4350 min ⁻¹
Battery capacity	8 Ah
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Power supply	Rechargeable battery-powered
Suitable for material	Concrete
Suitable for material	Stone
Suitable for material	Masonry
Type of product	Hammer drill

Accessories

Li-ion battery Battery type, battery voltage B18 V	073854 B18
Battery starter setProCore Battery type, battery voltage C18 V	073865 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073857 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073856 C18
Li-ion battery Battery type, battery voltage B18 V	073851 B18

Li-ion batteryProCore Battery type, battery voltage C18 V	073858 C18
Li-ion battery Battery type, battery voltage B18 V	073853 B18
Battery starter setProCore Battery type, battery voltage C18 V	073867 C18
Battery charger Type 1880CV	073866 1880CV
Battery starter setProCore Battery type, battery voltage C18 V	073863 C18