



## Screwdriver set, Number of screwdrivers: 13



### Order data

Order number	667270 13
GTIN	4013288176349
Item class	63H

### Description

#### Version:

**Handle** of impact resistant plastic with integral soft zones. Impact cap and wrench assistance (apart from slot-head size 3.5). Hexagon **blade** of special steel, through to the end of the handle. (Size 3.5 not through).

#### Supplied with:

13 pieces in 2 plastic clips.

1 each slot-head screwdriver No. 660300 size 3.5; 4.5; 5.5; 7; 9.

1 each screwdriver for Phillips No. 668300 size 1; 2; 3.

1 each Pozidriv screwdriver No. 668305 size 1; 2; 3.

1 each screwdriver for Torx® size TX20; TX25.

### Technical description

Actuation hexagon	yes
Number of screwdrivers	13
Drive profile	Screwdriver for Phillips
Drive profile	Slot-head screwdriver
Drive profile	Pozidriv screwdriver

Drive profile	Screwdriver for TORX® screws
Manufacturer's designation	Big Pack 900
Impact cap	true, apart from slot-head size 3.5
Type of handle	Impact-resistant plastic with integral soft zone (except slot-head size 3.5)
Material of handle	impact resistant plastic
through blade	yes
Type of product	Screwdriver

## Accessories

Screwdriver for slot-head, with Kraftform handle and impact cap Blade width b 7 mm	660300 7
Screwdriver for slot-head, with Kraftform handle and impact cap Blade width b 5,5 mm	660300 5,5
Screwdriver for slot-head, with Kraftform handle and impact cap Blade width b 3,5 mm	660300 3,5
Screwdriver for Phillipswith impact cap Cross-head size 2	668300 2
Screwdriver for Phillipswith impact cap Cross-head size 3	668300 3
Screwdriver for slot-head, with Kraftform handle and impact cap Blade width b 4,5 mm	660300 4,5
Screwdriver for Pozidrivwith impact cap Cross-head size 3	668305 3
Magnetiser	666450
Screwdriver for Pozidrivwith impact cap Cross-head size 1	668305 1
Screwdriver for Phillipswith impact cap Cross-head size 1	668300 1
Screwdriver for Pozidrivwith impact cap Cross-head size 2	668305 2
Screwdriver for slot-head, with Kraftform handle and impact cap Blade width b 9 mm	660300 9