



Cordless multi-material cutter, Type: M12FCOT-0



Order data

Order number	078204 M12FCOT-0
GTIN	4058546225636
Item class	03L

Description

Version:

FUEL **cordless multi-material cutter** with 76 mm blade for 16.3 mm depth of cut.

Supplied with:

Without battery and without charger. 1 × diamond disc for tiles, 1 × carbide abrasive disc, 1 × metal cutting wheel, 1 × adjustable dust extraction.

Note:

For matching spare batteries and accessories see from No. 073814.

For a suitable cutting disc see No. 563050 size 75.

Technical description

suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Manufacturer's designation	M12FCOT-0
Weight	1 kg
Saw blade bore Ø	10 mm
Battery voltage	12 V

maximum vibration to EN	2.9 m/s ²
maximum speed	20000 min ⁻¹
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	0
maximum cutting depth	16.3 mm
maximum disc Ø	76 mm
Power supply	Rechargeable battery-powered
Type of product	Saw

Accessories

Battery starter set Type M12NRG4	073839 M12NRG4
Small cutting discPREMIUM*** EXTRA THIN Disc Ø 75 mm	563050 75
Battery charger Type M1218C	073840 M1218C
Li-ion system M12B6 Battery type MB12	073829 MB12
Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
Li-ion system M12B4 Battery type MB12	073815 MB12
Battery charger Type M1218FC	073840 M1218FC