

Garant**Socket set 3/8 inch, Number of tools: 13****Order data**

Order number	953690 13
GTIN	4062406155681
Item class	91A

Description**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 953690: 1 pc.

GARANT ratchet No. 635025 size 3/8: 1 pc.

GARANT extension No. 635429 size 125: 1 pc.

GARANT universal joint No. 636229 size 3/8: 1 pc.

GARANT hexagon socket No. 637125 size 10; 11; 12; 13; 14; 15; 16; 17; 18; 19: 1 pc. each

Technical description

Weight	0.763 kg
Width	200 mm
Depth in G	8
Width in G	8

Number of tools	13
Depth	200 mm
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8×8
Square drive	3/8 in
Type of product	Rigid foam inlay

Accessories

Hexagon socket, 3/8 inchSurface Drive Width across flats 11 mm	637125 11
Hexagon socket, 3/8 inchSurface Drive Width across flats 12 mm	637125 12
Hexagon socket, 3/8 inchSurface Drive Width across flats 16 mm	637125 16
Reversible ratchet, 3/8 inch with ejector Type 3/8	635025 3/8
Hexagon socket, 3/8 inchSurface Drive Width across flats 19 mm	637125 19
Hexagon socket, 3/8 inchSurface Drive Width across flats 15 mm	637125 15
Hexagon socket, 3/8 inchSurface Drive Width across flats 14 mm	637125 14
Hexagon socket, 3/8 inchSurface Drive Width across flats 17 mm	637125 17
Extension, 3/8 inch overall length 125 mm	635429 125
Rigid foam inlay for tool sets suitable for rigid foam set 953690	952001 953690
Hexagon socket, 3/8 inchSurface Drive Width across flats 18 mm	637125 18
Universal joint, 3/8 inch Type 3/8	636229 3/8
	637125 10

Hexagon socket, 3/8 inchSurface Drive Width across flats
10 mm

Hexagon socket, 3/8 inchSurface Drive Width across flats
13 mm

637125 13