

**Garant**
**Socket set 1/4 inch and 1/2 inch, Number of tools: 37**

**Order data**

Order number	953828 37
GTIN	4062406155711
Item class	91A

**Description**
**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

**Supplied with:**

Rigid foam inlay, empty No. 952001 size 953828: 1 pc.

GARANT hexagon socket 1/4 inch No. 631029 size 4; 5; 5.5; 6; 7; 8; 9; 10; 11; 12: 1 pc. each

GARANT reversible ratchet, 1/4 inch No. 632025 size 1/4: 1 pc.

GARANT extension 1/4 inch No. 632429 size 50; 150: 1 pc. each

GARANT T-handle 1/4 inch No. 633029 size 116: 1 pc.

GARANT universal joint 1/4 inch No. 633529 size 1/4: 1 pc.

GARANT reversible ratchet, 1/2 inch No. 640025 size 1/2: 1 pc.

GARANT extension 1/2 inch No. 641029 size 75; 250: 1 pc. each

GARANT T-handle 1/2 inch No. 641329 size 295: 1 pc.

GARANT universal joint 1/2 inch No. 641629 size 1/2: 1 pc.

GARANT bi-hex socket 1/2 inch No. 642129 size 13; 16; 17; 18; 19; 21; 22; 24; 27: 1 pc. each

GARANT hexagon screwdriver bit 1/2 inch No. 643229 size 4; 5; 6; 7; 8; 10; 12; 14: 1 pc. each

**Technical description**

Depth in G	20
Weight	3.513 kg

Width	250 mm
Width in G	10
Depth	500 mm
Number of tools	37
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×20
Square drive	1/4 in
Square drive	1/2 in
Type of product	Rigid foam inlay

## Accessories

T-handle, 1/4 inch overall length 116 mm	633029 116
Extension, 1/2 inch overall length 255 mm	641029 255
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 7 mm	643229 7
Bi-hexagon socket, 1/2 inch Width across flats 27 mm	642129 27
Bi-hexagon socket, 1/2 inch Width across flats 19 mm	642129 19
Universal joint 1/4 inch Type 1/4	633529 1/4
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 4 mm	643229 4
T-handle, 1/2 inch overall length 295 mm	641329 295
Bi-hexagon socket, 1/2 inch Width across flats 22 mm	642129 22
Hexagon socket, 1/4 inch Width across flats 5 mm	631029 5
Extension, 1/4 inch overall length 50 mm	632429 50
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 10 mm	643229 10
Hexagon socket, 1/4 inch Width across flats 7 mm	631029 7
Hexagon socket, 1/4 inch Width across flats 11 mm	631029 11

Bi-hexagon socket, 1/2 inch Width across flats 17 mm	642129 17
Bi-hexagon socket, 1/2 inch Width across flats 18 mm	642129 18
Hexagon socket, 1/4 inch Width across flats 9 mm	631029 9
Rigid foam inlay for tool sets suitable for rigid foam set 953828	952001 953828
Bi-hexagon socket, 1/2 inch Width across flats 24 mm	642129 24
Hexagon socket, 1/4 inch Width across flats 10 mm	631029 10
Hexagon socket, 1/4 inch Width across flats 12 mm	631029 12
Hexagon socket, 1/4 inch Width across flats 8 mm	631029 8
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 8 mm	643229 8
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 6 mm	643229 6
Reversible ratchet, 1/2 inch with ejector Type 1/2	640025 1/2
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631029 5,5
Universal joint, 1/2 inch Type 1/2	641629 1/2
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 5 mm	643229 5
Bi-hexagon socket, 1/2 inch Width across flats 16 mm	642129 16
Hexagon socket, 1/4 inch Width across flats 4 mm	631029 4
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 14 mm	643229 14
Bi-hexagon socket, 1/2 inch Width across flats 21 mm	642129 21
Bi-hexagon socket, 1/2 inch Width across flats 13 mm	642129 13
Extension, 1/2 inch overall length 75 mm	641029 75
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 12 mm	643229 12
Extension, 1/4 inch overall length 150 mm	632429 150
Reversible ratchet, 1/4 inch with ejector Type 1/4	632025 1/4
Hexagon socket, 1/4 inch Width across flats 6 mm	631029 6