

**Garant****Soft-Pad roll soft, 100 mm × 24 m, Grit: 60****Order data**

Order number	557460 60
GTIN	4062406154486
Item class	51E

**Description****Version:**

Soft-Pad roll coated on one side with **standard aluminium oxide (A)**. **Ceramic coating** for a longer working life. Stored in a handy dispenser box, with visibility slot for quick assessment of the fill level.

**Advantage:**

**Pure foam backing material.** This achieves the greatest flexibility and resistance to grit break-away. Reduced alien material penetration into the workpiece surface by a bonding structure free of solvents. **200 perforated pads**, each 100×120×3 mm.

**Application:**

**Finish grinding of contours, edges, and at inaccessible places**, e.g. cleaning and preparation for painting. For wet and dry grinding.

**Technical description**

Grit	60
Grit designation	medium
Grinding media	Standard aluminium oxide (A)

Grinding medium code	A
Width	100 mm
Height	3 mm
Length	120 mm
Product name attribute	100 mm × 24 m
Number of coated surfaces	1
Number of sponges, pads	200
Type of product	Abrasive sanding sponge

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable		

dry

suitable