



High feed rate milling cutter MFH mini, with thread, Ø D / number of teeth Z: 20/3mm



Order data

Order number	221960 20/3
GTIN	4960664741069
Item class	250

Technical description

Insert screw	229713 (8IP; 1.2 Nm)
maximum cutting depth $a_{p\max}$	1 mm
suitable indexable insert	LOGU 0303..
Number of cutting edges Z	3
Overall length L_{tot}	30 mm
Cutting edge $\varnothing D_c$	20 mm
$\varnothing D_3$	13 mm
Mounting thread M	M10
Through-coolant	yes
Ramping length L for α_{\max}	11.3 mm
Circular interpolation milling $\varnothing D_{\min}$	33 mm
Ramping angle α_{\max}	1.52 degrees
Circular interpolation milling $\varnothing D_{\max}$	38 mm
Shank type	with thread

Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

Accessories

Clamping screw	229713
----------------	--------