

Garant
Hammer set, Number of tools: 3

Order data

Order number	954690 3
GTIN	2050002004399
Item class	91A

Description
Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer anthracite**, under which the **contrast colour** of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 10 G or 250 × 250 mm) or 1/2 (10 G × 20 G or 250 × 500 mm) of the usable drawer area.

Suitable for :

New GARANT GridLine workbenches with full extension drawers and a new drawer module of 20 G × 20 G or 500 × 500 mm (W × D).

Supplied with:

Rigid foam inlay, empty No. 952001 size 954690: 1 pc.

GARANT engineer's hammer No. 750110 size 300; 500: 1 pc. each

GARANT dead-blow plastic hammer No. 754750 size 40: 1 pc.

Degree of fill of a drawer in units: 10×20

Width: 250 mm

Depth: 500 mm

Width in G: 10

Depth in G: 20

Technical description

Number of tools	3
Width	250 mm

Width in G	10
Depth	500 mm
Depth in G	20
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×20
Type of product	Rigid foam inlay

Accessories

Dead-blow hammer with nylon inserts Hickory handle Hammer head Ø 40 mm	754750 40
Rigid foam inlay for tool sets suitable for rigid foam set 954690	952001 954690
Engineer's hammer with handle protection collar Weight without handle 300 g	750110 300
Engineer's hammer with handle protection collar Weight without handle 500 g	750110 500