

## Marking out, drilling, deburring, Number of tools: 4



### Order data

Order number	954858 4
GTIN	2050002004467
Item class	91A

### Description

#### Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

#### Supplied with:

Rigid foam inlay, empty No. 952001 size 954858: 1 pc.

GARANT jobber drill set HSS No. 115120 size 1 – 13: 1 pc.

GARANT hand deburrer 90° No. 150400 size 12.4: 1 pc.

HOLEX carbide scribe No. 458800: 1 pc.

Centre punch special quality No. 748900 size 120/10: 1 pc.

Smallest suitable drawer front height: 100 mm

Width: 200 mm

Depth: 250 mm

Width in G: 8

Depth in G: 10

### Technical description

Width in G	8
Depth	250 mm

Width	200 mm
Number of tools	4
Depth in G	10
Version	with tool kit
Weight	1.39 kg
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8×10
Smallest suitable drawer front height	100 mm
Type of product	Rigid foam inlay

---

## Accessories

Hand deburrer 90° External Ø 12,4 mm	150400 12,4
Jobber drill set HSS No. 114150 in a case Type 1-13	115120 1-13
Rigid foam inlay for tool sets suitable for rigid foam set 954858	952001 954858
Centre punch, special quality, chrome-plated overall length 120/10 mm	748900 120/10
Straight carbide scriber	458800