

**Garant**
**Pliers set, fully insulated, Number of tools: 3**

**Order data**

Order number	954515 3
GTIN	4062406157791
Item class	91A

**Description**
**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

**Supplied with:**

Rigid foam inlay, empty No. 952001 size 954515: 1 pc.

GARANT vanadium combination pliers No. 701710 size 180: 1 pc.

GARANT snipe-nose pliers No. 713310 size 200: 1 pc.

GARANT side cutter No. 725310 size 160: 1 pc.

Degree of fill of a drawer in units: 8×10

Width: 200 mm

Depth: 250 mm

Width in G: 8

Depth in G: 10

**Technical description**

Number of tools	3
Number of tools	3

Depth	250 mm
Depth in G	10
Width	200 mm
Width in G	8
Version	with VDE tool fully insulated
Weight	0.884 kg
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8×10
Type of product	Rigid foam inlay

---

## Accessories

Diagonal side cutter, chrome-plated VDE insulated overall length 160 mm	725310 160
Rigid foam inlay for tool sets suitable for rigid foam set 954515	952001 954515
Snipe nose pliers, straight VDE insulated overall length 200 mm	713310 200
Vanadium steel combination pliers, chrome-plated VDE insulated overall length 180 mm	701710 180