

**Garant**
**Socket set 3/8 inch, Number of tools: 24**

**Order data**

Order number	953707 24
GTIN	4062406157128
Item class	91A

**Description**
**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer anthracite, under which the contrast colour of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

**Suitable for:**

**New GARANT roller cabinets** with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Foam inlays of size 10 G × 8 G suit shadowboards No. 923210 size 250 (2 foam inlays per shadowboard).

**Supplied with:**

Rigid foam inlay, empty No. 952001 size 953707: 1 pc.

GARANT hexagon socket No. 637125 size 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19: 1 pc. each

GARANT hexagon screwdriver bit No. 637629 size 3; 4; 5; 6; 7; 8; 10: 1 pc. each

GARANT reversible ratchet, No. 635025 size 3/8: 1 pc.

GARANT extension No. 635429 size 75; 125: 1 pc. each

GARANT T-handle No. 635729 size 200: 1 pc.

GARANT universal joint No. 636229 size 3/8: 1 pc.

**Technical description**

Width in G	8
Weight	1.318 kg
Depth	250 mm
Number of tools	24
Depth in G	10
Width	200 mm
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8×10
Square drive	3/8 in
Type of product	Rigid foam inlay

## Accessories

Screwdriver socket, hexagon, 3/8 inch Hexagon 3 mm	637629 3
Hexagon socket, 3/8 inch Surface Drive Width across flats 14 mm	637125 14
Reversible ratchet, 3/8 inch with ejector Type 3/8	635025 3/8
Hexagon socket, 3/8 inch Surface Drive Width across flats 15 mm	637125 15
Hexagon socket, 3/8 inch Surface Drive Width across flats 13 mm	637125 13
Hexagon socket, 3/8 inch Surface Drive Width across flats 11 mm	637125 11
Universal joint, 3/8 inch Type 3/8	636229 3/8
Screwdriver socket, hexagon, 3/8 inch Hexagon 6 mm	637629 6
Hexagon socket, 3/8 inch Surface Drive Width across flats 19 mm	637125 19
Hexagon socket, 3/8 inch Surface Drive Width across flats 16 mm	637125 16
	637125 8

Hexagon socket, 3/8 inch Surface Drive Width across flats 8 mm	
Hexagon socket, 3/8 inch Surface Drive Width across flats 9 mm	637125 9
Screwdriver socket, hexagon, 3/8 inch Hexagon 4 mm	637629 4
Extension, 3/8 inch overall length 75 mm	635429 75
Hexagon socket, 3/8 inch Surface Drive Width across flats 10 mm	637125 10
Hexagon socket, 3/8 inch Surface Drive Width across flats 12 mm	637125 12
Hexagon socket, 3/8 inch Surface Drive Width across flats 7 mm	637125 7
T-handle, 3/8 inch overall length 200 mm	635729 200
Hexagon socket, 3/8 inch Surface Drive Width across flats 17 mm	637125 17
Hexagon socket, 3/8 inch Surface Drive Width across flats 18 mm	637125 18
Screwdriver socket, hexagon, 3/8 inch Hexagon 7 mm	637629 7
Rigid foam inlay for tool sets suitable for rigid foam set 953707	952001 953707
Extension, 3/8 inch overall length 125 mm	635429 125
Screwdriver socket, hexagon, 3/8 inch Hexagon 5 mm	637629 5
Screwdriver socket, hexagon, 3/8 inch Hexagon 10 mm	637629 10
Screwdriver socket, hexagon, 3/8 inch Hexagon 8 mm	637629 8