


**Garant**
**Pliers set, fully insulated, Number of tools: 5**

**Order data**

Order number	954537 5
GTIN	4062406157760
Item class	91A

**Description**
**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

**Supplied with:**

Rigid foam inlay, empty No. 952001 size 954537: 1 pc.  
 GARANT vanadium combination pliers No. 701710 size 180: 1 pc.  
 GARANT snipe-nose pliers No. 713310 size 200: 1 pc.  
 GARANT snipe-nose pliers, angled No. 713710 size 200: 1 pc.  
 GARANT side cutter No. 725310 size 160: 1 pc.  
 GARANT wire stripper No. 728755 size 160: 1 pc.

**Technical description**

Depth in G	20
Number of tools	5
Width	200 mm
Depth	500 mm
Number of tools	5
Width in G	8
Version	with VDE tool fully insulated

Weight	1.433 kg
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8x20
Type of product	Rigid foam inlay

## Accessories

Snipe nose pliers, angledVDE insulated overall length 200 mm	713710 200
Diagonal side cutter, chrome-platedVDE insulated overall length 160 mm	725310 160
Vanadium steel combination pliers, chrome-platedVDE insulated overall length 180 mm	701710 180
Wire stripping tool chrome-platedVDE insulated overall length 160 mm	728755 160
Rigid foam inlay for tool sets suitable for rigid foam set 954537	952001 954537
Snipe nose pliers, straightVDE insulated overall length 200 mm	713310 200