

Marking out and sawing, Number of tools: 8



Order data

Order number	954890 8
GTIN	2050002004504
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 954890: 1 pc.
EDDING permanent marker No. 085130 size R: 1 pc.
GARANT caliper No. 410100 size 150: 1 pc.
Carbide scribe No. 458760 size HM: 1 pc.
HOLEX precision steel rule No. 461600 size 300: 1 pc.
GARANT steel tape measure No. 461992 size 3: 1 pc.
Pocket spirit level No. 467482 size 70: 1 pc.
GARANT hacksaw frame No. 580400: 1 pc.
GARANT hacksaw blades No. 582500 (pack of 10): 1 pc.

Technical description

Width	200 mm
Width in G	8
Depth in G	20
Depth	500 mm

Number of tools	8
Version	with tool kit
Weight	1.474 kg
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8x20
Type of product	Rigid foam inlay

Accessories

Straight carbide scriber with clip and protective cap Type	458760
Hacksaw framewith GARANT bimetal blade 18 – 32 TPI progressive	580400
Permanent marker Writing colour R	085130 R
Engineer's precision steel rule stainless, matt finished Length 300 mm	461600 300
Hacksaw blade, single-sided bimetal, progressive	582500
Rigid foam inlay for tool sets suitable for rigid foam set 954890	952001 954890
Vernier caliper Measuring range 150 mm	410100 150
Steel tape measure "Quickmeter" Band length 3 m	461992 3
Pocket spirit level Pro Magnetic Length 70 mm	467482 70