


Garant

Double open ended spanner set, Number of tools: 8



Order data

Order number	955115 8
GTIN	4062406157920
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 955115: 1 pc.

GARANT double open ended spanner No. 610600 size 4×5; 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19: 1 pc. each

Technical description

Width	383 mm
Depth	115 mm
Version	with spanners (ring spanners and open-ended spanners)
Rigid foam quality LD45, thickness	30 mm
suitable for shadowboard depth	115 mm
Type of product	Rigid foam inlay

Accessories

Double open ended spanner Jaw widths 12X13 mm	610600 12X13
Double open ended spanner Jaw widths 14X15 mm	610700 14X15
Double open ended spanner Jaw widths 8X9 mm	610600 8X9
Double open ended spanner Jaw widths 16X17 mm	610700 16X17
Double open ended spanner Jaw widths 16X17 mm	610600 16X17
Double open ended spanner Jaw widths 10X11 mm	610600 10X11
Rigid foam inlay for tool sets suitable for rigid foam set 955115	952001 955115
Double open ended spanner Jaw widths 14X15 mm	610600 14X15
Double open ended spanner Jaw widths 4X5 mm	610600 4X5
Double open ended spanner Jaw widths 6X7 mm	610600 6X7
Double open ended spanner Jaw widths 18X19 mm	610700 18X19
Double open ended spanner Jaw widths 18X19 mm	610600 18X19