

Garant
Socket set 3/8 inch, Number of tools: 37

Order data

Order number	953741 37
GTIN	2050002004276
Item class	91A

Description
Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer anthracite, under which the contrast colour of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

Suitable for:

New GARANT roller cabinets with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Supplied with:

Rigid foam inlay, empty No. 952001 size 953741: 1 pc.

GARANT hexagon socket No. 637125 size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24: 1 pc. each

GARANT screwdriver bit for Torx® No. 637560 size TX9; TX10; TX15; TX20; TX25; TX27; TX30; TX40; TX45: 1 pc. each

GARANT hexagon screwdriver bit No. 637629 size 3; 4; 5; 6; 7; 8; 10: 1 pc. each

GARANT reversible ratchet, No. 635025 size 3/8: 1 pc.

GARANT extension No. 635429 size 75; 125; 240: 1 pc. each

GARANT T-handle No. 635729 size 200: 1 pc.

GARANT universal joint No. 636229 size 3/8: 1 pc.

Technical description

Width	200 mm
-------	--------

Depth	500 mm
Width in G	8
Weight	2.211 kg
Depth in G	20
Number of tools	37
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8x20
Square drive	3/8 in
Type of product	Rigid foam inlay

Accessories

Extension, 3/8 inch overall length 75 mm	635429 75
Universal joint, 3/8 inch Type 3/8	636229 3/8
Screwdriver socket, hexagon, 3/8 inch Hexagon 6 mm	637629 6
Hexagon socket, 3/8 inch Surface Drive Width across flats 19 mm	637125 19
Screwdriver socket, for Torx®, 3/8 inch short Torx® profile TX20	637560 TX20
Screwdriver socket, hexagon, 3/8 inch Hexagon 7 mm	637629 7
Screwdriver socket, for Torx®, 3/8 inch short Torx® profile TX9	637560 TX9
Hexagon socket, 3/8 inch Surface Drive Width across flats 21 mm	637125 21
Screwdriver socket, for Torx®, 3/8 inch short Torx® profile TX15	637560 TX15
Hexagon socket, 3/8 inch Surface Drive Width across flats 11 mm	637125 11
Rigid foam inlay for tool sets suitable for rigid foam set 953741	952001 953741

Reversible ratchet, 3/8 inch with ejector Type 3/8	635025 3/8
Screwdriver socket, hexagon, 3/8 inch Hexagon 8 mm	637629 8
Hexagon socket, 3/8 inch Surface Drive Width across flats 22 mm	637125 22
T-handle, 3/8 inch overall length 200 mm	635729 200
Extension, 3/8 inch overall length 240 mm	635429 240
Hexagon socket, 3/8 inch Surface Drive Width across flats 16 mm	637125 16
Hexagon socket, 3/8 inch Surface Drive Width across flats 24 mm	637125 24
Hexagon socket, 3/8 inch Surface Drive Width across flats 8 mm	637125 8
Screwdriver socket, hexagon, 3/8 inch Hexagon 3 mm	637629 3
Hexagon socket, 3/8 inch Surface Drive Width across flats 13 mm	637125 13
Hexagon socket, 3/8 inch Surface Drive Width across flats 10 mm	637125 10
Hexagon socket, 3/8 inch Surface Drive Width across flats 12 mm	637125 12
Screwdriver socket, hexagon, 3/8 inch Hexagon 4 mm	637629 4
Screwdriver socket, for Torx®, 3/8 inch short Torx® profile TX30	637560 TX30
Hexagon socket, 3/8 inch Surface Drive Width across flats 15 mm	637125 15
Screwdriver socket, hexagon, 3/8 inch Hexagon 10 mm	637629 10
Screwdriver socket, for Torx®, 3/8 inch short Torx® profile TX25	637560 TX25
Screwdriver socket, for Torx®, 3/8 inch short Torx® profile TX45	637560 TX45
Hexagon socket, 3/8 inch Surface Drive Width across flats 18 mm	637125 18
Extension, 3/8 inch overall length 125 mm	635429 125
Hexagon socket, 3/8 inch Surface Drive Width across flats 9 mm	637125 9

Screwdriver socket, for Torx®, 3/8 inchshort Torx® profile TX40	637560 TX40
Screwdriver socket, for Torx®, 3/8 inchshort Torx® profile TX27	637560 TX27
Hexagon socket, 3/8 inchSurface Drive Width across flats 14 mm	637125 14
Screwdriver socket, hexagon, 3/8 inch Hexagon 5 mm	637629 5
Screwdriver socket, for Torx®, 3/8 inchshort Torx® profile TX10	637560 TX10
Hexagon socket, 3/8 inchSurface Drive Width across flats 17 mm	637125 17