

Marking out and sawing, Number of tools: 8



Order data

Order number	954895 8
GTIN	2050002004511
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 954895: 1 pc.
 EDDING permanent marker No. 085130 size B: 1 pc.
 HOLEX try square No. 452600 size 300×175: 1 pc.
 HOLEX protractor No. 453000 size 120×150: 1 pc.
 PB straight carbide scribe No. 458760 size HM: 1 pc.
 HOLEX precision steel rule No. 461600 size 300: 1 pc.
 GARANT tape measure No. 462201 size 2.5: 1 pc.
 GARANT hacksaw frame No. 580400: 1 pc.
 GARANT hacksaw blades No. 582500 (pack of 10): 1 pc.

Technical description

Depth	500 mm
Depth in G	20
Width in G	10
Width	250 mm
Number of tools	8

Version	with tool kit
Weight	2.476 kg
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×20
Type of product	Rigid foam inlay

Accessories

Engineer's precision steel rule stainless, matt finished Length 300 mm	461600 300
Hacksaw frame with GARANT bimetal blade 18 – 32 TPI progressive	580400
Hacksaw blade, single-sided bimetal, progressive	582500
Permanent marker Writing colour B	085130 B
Try square Accuracy class 2 Stock length 300X175 mm	452600 300X175
Tape measure with viewing window Band length 2,5 m	462201 2,5
Rigid foam inlay for tool sets suitable for rigid foam set 954895	952001 954895
Protractor with open graduated arc Graduated arc Ø×Stock length 120X150 mm	453000 120X150
Straight carbide scriber with clip and protective cap Type	458760