

Garant
Socket set 1/2 inch, Number of tools: 30

Order data

Order number	953747 30
GTIN	4062406157234
Item class	91A

Description
Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer anthracite, under which the contrast colour of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

Suitable for:

New GARANT roller cabinets with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Supplied with:

Rigid foam inlay, empty No. 952001 size 953747: 1 pc.

GARANT hexagon socket No. 642325 size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32: 1 pc. each

GARANT hexagon screwdriver bit No. 643229 size 4; 5; 6; 8; 10; 12; 14: 1 pc. each

GARANT reversible ratchet, No. 640025 size 1/2: 1 pc.

GARANT extension No. 641029 size 75; 125; 250: 1 pc. each

GARANT T-handle No. 641329 size 295: 1 pc.

GARANT universal joint No. 641629 size 1/2: 1 pc.

Technical description

Depth	500 mm
Number of tools	30

Number of tools	30
Width in G	8
Depth in G	20
Width	200 mm
Weight	3.891 kg
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8x20
Square drive	1/2 in
Type of product	Rigid foam inlay

Accessories

Surface Drive hexagon socket, 1/2 inch Width across flats 19 mm	642325 19
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 12 mm	643229 12
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 8 mm	643229 8
Extension, 1/2 inch overall length 255 mm	641029 255
Extension, 1/2 inch overall length 75 mm	641029 75
Reversible ratchet, 1/2 inch with ejector Type 1/2	640025 1/2
Universal joint, 1/2 inch Type 1/2	641629 1/2
Surface Drive hexagon socket, 1/2 inch Width across flats 13 mm	642325 13
Extension, 1/2 inch overall length 130 mm	641029 130
Surface Drive hexagon socket, 1/2 inch Width across flats 11 mm	642325 11
Surface Drive hexagon socket, 1/2 inch Width across flats 10 mm	642325 10
	643229 5

Screwdriver socket, inside hexagon, 1/2 inch Hexagon 5 mm	
Surface Drive hexagon socket, 1/2 inch Width across flats 22 mm	642325 22
Surface Drive hexagon socket, 1/2 inch Width across flats 12 mm	642325 12
Surface Drive hexagon socket, 1/2 inch Width across flats 17 mm	642325 17
T-handle, 1/2 inch overall length 295 mm	641329 295
Surface Drive hexagon socket, 1/2 inch Width across flats 18 mm	642325 18
Rigid foam inlay for tool sets suitable for rigid foam set 953747	952001 953747
Surface Drive hexagon socket, 1/2 inch Width across flats 14 mm	642325 14
Surface Drive hexagon socket, 1/2 inch Width across flats 21 mm	642325 21
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 10 mm	643229 10
Surface Drive hexagon socket, 1/2 inch Width across flats 8 mm	642325 8
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 4 mm	643229 4
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 6 mm	643229 6
Surface Drive hexagon socket, 1/2 inch Width across flats 27 mm	642325 27
Surface Drive hexagon socket, 1/2 inch Width across flats 15 mm	642325 15
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 14 mm	643229 14
Surface Drive hexagon socket, 1/2 inch Width across flats 30 mm	642325 30
Surface Drive hexagon socket, 1/2 inch Width across flats 16 mm	642325 16

Surface Drive hexagon socket, 1/2 inch Width across flats
24 mm

642325 24

Surface Drive hexagon socket, 1/2 inch Width across flats
32 mm

642325 32

Reversible ratchet, 1/2 inch with ejector Type

640025