

Trainee mechanical fitter's tool kit, 43 pieces for industrial mechanics without folding box, Number of tools: 43



Order data

Order number	680265 43
GTIN	2050002003576
Item class	66H

Description

Supplied with:

Magnetic holder: 3 pc. No. 085915 size 20

GARANT calipers: 1 pc. No. 410100 size 150

Try squares: 1 pc. No. 452600 size 100×70

Precision spring dividers: 1 pc. No. 457000 size 150

Scriber, straight: 1 pc. No. 458500

Steel rule: 1 pc. No. 461805 size 300

GARANT locking tape measure: 1 pc. No. 462210 size 2

Hand file, bastard cut: 1 pc. each No. 510100 size 150; 250

DICK hand file, cut 3 (smooth): 1 pc. each No. 510300 size 150; 250

DICK three-square file, cut 1 (bastard): 1 pc. No. 511100 size 250

DICK three-square file, cut 3 (smooth): 1 pc. No. 511300 size 200

DICK square file, cut 1 (bastard): 1 pc. No. 512100 size 250

DICK square file, cut 3 (smooth): 1 pc. No. 512300 size 150

DICK round file, cut 1 (bastard): 1 pc. No. 514100 size 250

DICK round file, cut 3 (smooth): 1 pc. No. 514300 size 200

Hardwood file handles: 2 pc. No. 519400 size 100, 5 pc. size 120 and 3 pc. size 140

File brush: 1 pc. No. 576000 size 115×40

GARANT slot-head screwdriver: 1 pc. No. 660030 size 5.5

PB Swiss Tools flat chisel: 1 pc. No. 740900 size 150

PB Swiss Tools taper pin punch: 1 pc. each No. 745300 size 3; 6

PB Swiss Tools centre punch: 1 pc. No. 748900 size 120
GARANT engineer's hammer: 1 pc. No. 750110 size 500
RENNSTEIG three-edge hollow scraper: 1 pc. No. 836010 size 200
RENNSTEIG flat scraper: 1 pc. No. 837020 size 250
GARANT vice jaws (pair): 1 pc. No. 967711 size 125
 Bench hand brush: 1 pc. No. 087553 size 280
uvex[®] comfort safety glasses, clear: 1 pc. No. 096504 size CLEAR
 Ear defenders: 1 pc. No. 097795 size STEEL
 Leather work gloves (pair): 1 pc. No. 094055 size 10

Note:**Supplied loose.**

Technical description

Type of product	tool set
-----------------	----------

Accessories

Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 5,5 mm	660030 5,5
Flat scraper Blade length 250 mm	837020 250
Hardwood file handle Overall length 120 mm	519400 120
Round file Length without tang 250 mm	514100 250
Three-edge hollow scraper Blade length 200 mm	836010 200
Hand file Length without tang 150 mm	510100 150
Spring dividers with points Length L 150 mm	457000 150
Hand file Length without tang 150 mm	510300 150
Taper pin punches, special quality chrome-plated Tip Ø 6 mm	745300 6
Engineer's hammer with handle protection collar Weight without handle 500 g	750110 500
Workbench hand brushes Polymer coconut fibre [®] Length 280 mm	087553 280
Centre punch, special quality, chrome-plated overall length 120/12 mm	748900 120/12

Safety glasses Lens tinting CLEAR	096804 CLEAR
Taper pin punches, special quality chrome-plated Tip Ø 3 mm	745300 3
Flat magnet with internal thread Ø 20 mm	085915 20
Hand file Length without tang 250 mm	510300 250
Tape measure with viewing window Band length 2 m	462210 2
Hand file Length without tang 250 mm	510100 250
Comfort safety glasses uvex pheos cx2 Lens tinting CLEAR	096504 CLEAR
Pair of light metal vice jaws with spring clips Jaw width 125 mm	967711 125
Straight scriber	458500
Square file Length without tang 150 mm	512300 150
Pair of gloves Full-grain leather Glove size 10	094055 10
Vernier caliper Measuring range 150 mm	410100 150
Safety glasses Lens tinting CLEAR	096807 CLEAR
Three square file Length without tang 200 mm	511300 200
Round file Length without tang 200 mm	514300 200
Three square file Length without tang 250 mm	511100 250
Centre punch, special quality, chrome-plated overall length 120/10 mm	748900 120/10
Square file Length without tang 250 mm	512100 250
File brush Bristle length L3× width L1 115X40 mm	576000 115X40
Try square Accuracy class 2 Stock length 100X70 mm	452600 100X70
Flat cold chisel overall length 150 mm	740900 150
Flexible steel rule narrow, stainless matt finished with graduations on rear Overall length 300 mm	461805 300
Hardwood file handle Overall length 100 mm	519400 100
Ear defenders Type STEEL	097795 STEEL
Ear defenders Bilsom® Viking® Type	097763
Spring dividers with points Length L 150 mm	457005 150