

**Garant**

**Roller cabinet incl. general-purpose tool selection, 174 pieces for 4 drawers, Type: 1**

**Order data**

Order number	689000 1
GTIN	4062406158927
Item class	61H

**Description****Version:**

Compact roller cabinet in the new GridLine range with 7 drawers, of which 4 are equipped with the high-quality professional tools supplied. Consisting of the following: Spanners, 1/2 inch socket spanners, screwdrivers, pliers, hammers, files, striking tools, bits, hexagon key I-wrenches and supplementary items. The contents of the other 3 drawers can be individually selected. The general-purpose tool selection fits precisely in two-tone PE rigid foam inlays, in which each tool has its own defined place in the roller cabinet.

The drawers of the roller cabinet are unlocked using a central catch integrated in the handle.

Each 75 mm drawer is supplied with 1 slotted partition No. 951510 size 75, each 125 mm drawer is supplied with 1 slotted partition No. 951510 size 125. If desired, the worktop can be exchanged for another worktop (such as a bamboo worktop).

**Version of the roller cabinet:**

- **Large area. Practical. Scratch-resistant and non-slip X-ABS worktop which does not damage surfaces.**
- **Systematic. Divisible. With 7 drawers, offers room for a large number of tools.**
- **Visual. Powerful. Two-tone powder-coated, silver combined with RAL 7016 anthracite.**
- **Mobile. Extremely sturdy. 2 each fixed wheels and 2 castors with brakes for reliable smooth running and stability.**

**Supplied with:**

Roller cabinet: 1 pc. No. 914540 size 7

Combination spanner set, 19 pieces: 1 pc. No. 952428 size 19

Screwdriver set, 13 pieces, for slot-head and Phillips screws: 1 pc. No. 953432 size 13

Socket set 1/2 inch, 30 pieces: 1 pc. No. 953747 size 30

Hammer set, 3 pieces: 1 each No. 750110 size 300; 500

1 pc. No. 752520 size 40G

Pliers set, 5 pieces: 1 pc. No. 954201 size 5

File set, 5 pieces: 1 pc. No. 517411 size 200

Hexagon key L-wrench set for Torx® and hexagon, 22 pieces: 1 pc. No. 953141 size 22

Chisel, taper pin punch, and pin punch set, 10 pieces: 1 pc. No. 954652 size 10

Workshop accessories set, 63 pieces: 1 pc. No. 676040

1 pc. No. 845020

1 pc. No. 763030 size 205

Measurement tool set, 4 pieces: 1 pc. No. 410100 size 150

1 pc. No. 461900 size 3

1 pc. No. 466200 size 2

1 pc. No. 081505 size 125

**Note:**

**Tools are supplied loose.**

**Other tool organiser systems for roller cabinets can be found from No. 952048. The equipped roller cabinet 689000 size 1 can be dispatched only to destinations within the EU.**

**Technical description**

Height	1000 mm
Drawer usable depth	400 mm
Width	800 mm
Number of drawers	7
Drawer usable width in G	20
Drawer usable depth in G	16
Drawer usable width	500 mm
Depth	500 mm
Individual drawer release system	One-hand
Drawer usable area in G	20×16
Drawer/pull-out shelf load capacity	40 kg
Drawer runner extension (partial/full extension)	100 %

Drawer runner extension	Anti-tilt lock
Hoffmann perforated panel grid interval	9×9 mm
Degree of fill of a drawer in units	8×10
Degree of fill of a drawer in units	8×20
Square drive	1/2 in
Cylinder lock	modular barrel
Components	equipped
Type of product	Roller cabinet

## Accessories

LED torcheswith batteries Type 130 mm	081505 130
Bit set61 pieces	676040
LED torcheswith batteries Type 125 mm	081505 125
Engineer's hammer withhandle protection collar Weight without handle 300 g	750110 300
Tape measure Length 3 m	461900 3
Screwdriver set Number of tools 13	953431 13
File set with 2-component handle, 5 pieces in a tool rollMetal Length without tang 200 mm	517411 200
General-purpose knife with 2-component handlewith 3 blades, 18 mm	845020
Combination spanner set Number of tools 19	952428 19
Pliers set Number of tools 5	954201 5
Soft-faced hammer with nylon inserts Housing Ø / material 40G mm	752520 40G
Chisel, taper pin punch, and pin punch set Number of tools 10	954652 10
L-wrenches for Torx® and hexagon key L-wrenches Number of tools 22	953141 22
Vernier caliper Measuring range 150 mm	410100 150

Engineer's hammer with handle protection collar Weight without handle 500 g	750110 500
Plastic folding rule Length 2 m	466200 2
Socket set 1/2 inch Number of tools 30	953747 30
Multi-purpose shears with 2-component handles straight, with adjustable handle opening overall length 205 mm	763030 205
Roller cabinet with full extension drawers Number of drawers 7	914540 7
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 2	667690 2
Pin punch, standard quality, painted Point Ø D 8 mm	747000 8
Flat chisel overall length 200 mm	740500 200
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 3,5 mm	660030 3,5
Side cutter chrome-plated, with grips overall length 160 mm	724840 160
Surface Drive hexagon socket, 1/2 inch Width across flats 13 mm	642325 13
Hexagon bit socket, 1/2 inch Hexagon 4 mm	643229 4
Rigid foam inlay for tool sets suitable for rigid foam set 953431	952001 953431
Water pump pliers with stepped fine adjustment, black overall length 250 mm	706001 250
Cross-cut chisel overall length 200 mm	740600 200
Hexagon bit socket, 1/2 inch Hexagon 10 mm	643229 10
Surface Drive hexagon socket, 1/2 inch Width across flats 22 mm	642325 22
Surface Drive hexagon socket, 1/2 inch Width across flats 27 mm	642325 27
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 4 mm	660030 4
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 2,5 mm	660030 2,5
	642325 16

Surface Drive hexagon socket, 1/2 inch Width across flats  
16 mm

Hexagon bit socket, 1/2 inch Hexagon 14 mm

643229 14

Pin punch, standard quality, painted Point Ø D 5 mm

747000 5

Rigid foam inlay for tool sets suitable for rigid foam set  
952428

952001 952428

Snipe nose pliers, angled, chrome-plated, with grips overall  
length 200 mm

713440 200

Surface Drive hexagon socket, 1/2 inch Width across flats  
12 mm

642325 12

Combination pliers, chrome-plated, with 2-component  
grips overall length 180 mm

700940 180

Taper pin punch heavy version Tip Ø 4 mm

745500 4

Taper pin punch heavy version Tip Ø 3 mm

745500 3

Surface Drive hexagon socket, 1/2 inch Width across flats  
32 mm

642325 32

Extension, 1/2 inch overall length 130 mm

641029 130

Hexagon bit socket, 1/2 inch Hexagon 12 mm

643229 12

Screwdriver for Phillips, with 2-component Haptoprene  
handle Cross-head size 3

667690 3

Screwdriver for slot-head, with 2-component Haptoprene  
handle Blade width b 6,5 mm

660030 6,5

Surface Drive hexagon socket, 1/2 inch Width across flats  
30 mm

642325 30

Screwdriver for Phillips, with 2-component Haptoprene  
handle Cross-head size 1

667690 1

Pin punch, standard quality, painted Point Ø D 2 mm

747000 2

Surface Drive hexagon socket, 1/2 inch Width across flats  
11 mm

642325 11

Surface Drive hexagon socket, 1/2 inch Width across flats  
21 mm

642325 21

Universal joint, 1/2 inch Type 1/2

641629 1/2

Rigid foam inlay for tool sets suitable for rigid foam set  
954201

952001 954201

Reversible ratchet, 1/2 inch with ejector Type 1/2	640025 1/2
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 0	667690 0
Rigid foam inlay for tool sets suitable for rigid foam set 953747	952001 953747
Torx® key L-wrench set, with MagicSpring® retainer function Number of screwdrivers 13	625025 13
Hexagon key L-wrench set, with retainer ballchrome-plated Number of screwdrivers 9	627132 9
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 10 mm	660030 10
Combination spanner set Number of keys 19	613610 19
Surface Drive hexagon socket, 1/2 inch Width across flats 24 mm	642325 24
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 5,5 mm	660030 5,5
Pin punch, standard quality, painted Point Ø D 6 mm	747000 6
Pin punch, standard quality, painted Point Ø D 3 mm	747000 3
Extension, 1/2 inch overall length 75 mm	641029 75
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 8 mm	660030 8
T-handle, 1/2 inch overall length 295 mm	641329 295
Rigid foam inlay for tool sets suitable for rigid foam set 953141	952001 953141
Hexagon bit socket, 1/2 inch Hexagon 5 mm	643229 5
Surface Drive hexagon socket, 1/2 inch Width across flats 19 mm	642325 19
Rigid foam inlay for tool sets suitable for rigid foam set 954652	952001 954652
Snipe nose pliers, straight, chrome-plated, with grips overall length 200 mm	713040 200
Hexagon bit socket, 1/2 inch Hexagon 6 mm	643229 6
Pin punch, standard quality, painted Point Ø D 4 mm	747000 4

Surface Drive hexagon socket, 1/2 inch Width across flats 17 mm	642325 17
Surface Drive hexagon socket, 1/2 inch Width across flats 15 mm	642325 15
Surface Drive hexagon socket, 1/2 inch Width across flats 8 mm	642325 8
Hexagon bit socket, 1/2 inch Hexagon 8 mm	643229 8
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 00	667690 00
Surface Drive hexagon socket, 1/2 inch Width across flats 10 mm	642325 10
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 2 mm	660030 2
Surface Drive hexagon socket, 1/2 inch Width across flats 18 mm	642325 18
Extension, 1/2 inch overall length 255 mm	641029 255
Surface Drive hexagon socket, 1/2 inch Width across flats 14 mm	642325 14
Lock plate for GridLine Type VA21	914227 VA21
Screwdriver set Number of tools 13	953432 13