

Garant GRIDLINE

**Pull-out shelf 75 kg, 26×20G, Installation height: 75mm****Order data**

Order number	930654 75
GTIN	4062406158934
Item class	9GK

**Description****Version:**

Pull-out shelf with **100% full extension**. Open in front, shell height at sides 46 mm, installation height 75 mm. Without slots to take slotted dividers.

**Suitable for:**

Auxiliary cabinet 30×28G.

**Supplied with:**

Pull-out shelves each complete with 1 pair drawer runner rails.

**Colour:**

Light grey RAL 7035, **powder-coated**.

**Note:**

Not suitable for fitting into mobile cabinets.

**Technical description**

Drawer usable area in G	26×20
Usable depth	500 mm
Usable depth in G	20
Usable width	650 mm
Usable width in G	26
Application range	Tool cabinet
with individual drawer release system	no
Installation height	75 mm

Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×20G
Type of product	Pull-out shelf