



ONE-KEY™ cordless hammer drill / driver, Type: M18OPD2-5



Order data

Order number	070102 M18OPD2-5
GTIN	4058546224721
Item class	03L

Description

Version:

- **Powerful cordless 2-speed hammer drill / driver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

FUEL™ ONE-KEY™ – latest generation of the FUEL™ devices with **integral Bluetooth technology for individual configuration, online stock management and device reporting.**

FUEL™ top model with high torque.

Supplied with:

Supplied with charger, transport case (HD box) and belt clip.

Note:

Suitable Bluetooth tracking modules can be found in the online shop under No. 070103 TICK. See No. 073814 et seqq. and 073840 for suitable batteries and chargers, and a suitable battery starter set can be found under No. 073839.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

App link: OneKey

Manufacturer's designation: M18ONEPD2-502X

Battery capacity: 5 Ah

Battery voltage: 18 V

Motor design: FUEL™

maximum torque: 135 Nm

maximum speed 1st speed: 0 - 550 rpm

Technical description

Battery capacity	5 Ah
maximum twist drill size Ø in steel	16 mm
Weight	2.2 kg
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 1st speed	0 - 550 rpm
maximum twist drill size Ø in concrete	16 mm
maximum torque	135 Nm
maximum vibration to EN without hammer drill function	1.33 m/s ²
Packaging	Modular case (HD=Heavy Duty)
maximum vibration to EN with hammer drill function	13.2 m/s ²
Battery voltage	18 V
App link	OneKey
typical application	Heavy Duty
Motor design	FUEL™
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum speed 2nd speed	2000 rpm
Manufacturer's designation	M18ONEPD2-502X
maximum twist drill size Ø in wood	89 mm
Power supply	Rechargeable battery-powered
Type of product	limpact drill /screwdriver

Accessories

Li-ion system M18B5 Rechargeable battery type, battery voltage MB18 V

073816 MB18

Li-ion battery High Output™ Battery type, battery voltage MHB55 V

073809 MHB55

Battery charger Type M1218C

073840 M1218C

Battery charger Type M1218FC

073840 M1218FC