

**Cordless drill/driver, Type: 7116116H1****Order data**

Order number	070200 7116116H1
GTIN	2050002046474
Item class	03F

Description**Version:****2 and 4 speed cordless drill/driver**

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

2-speed cordless impact drill / driver with brushless motor.

- Low-maintenance, POWER-Drive EC motor with high torque, and overload protection.
- Mechanical stage torque setting, adjustable in 22 steps, additional drilling step.
- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.

- **Li-ion batteries with high current capability, single-cell monitoring, and capacity display.**

Advantage:

With QuickIN MAX interface.

Supplied with:

Supplied with 2× 18 V Li-ion batteries, drill chuck, charger, belt clip, carrying case.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

Quick-clamping chuck range	1.5 - 13 mm
Motor design	Brushless motor
maximum speed 1st speed	400 min ⁻¹
maximum twist drill size Ø in steel	25 mm
maximum torque hard	90 Nm
maximum vibration to EN	<2.5 m/s ²
maximum speed 2nd speed	800 min ⁻¹
maximum twist drill size Ø in wood	50 mm
maximum speed 3rd speed	1950 min ⁻¹
Battery voltage	18 V
Manufacturer's designation	ASCM 18 QM
Weight	2 kg
maximum torque soft	46 Nm
Packaging	Carrying case
maximum speed 4th speed	3850 min ⁻¹
Number of rechargeable batteries contained	2
suitable battery - supplier / battery type / voltage	Fein type E 18 V
typical application	Heavy Duty
Battery capacity	6 Ah
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered

Suitable for material	Steel
Suitable for material	wood
Type of product	Drill/driver
USP1	4-speed gearbox. 18V
USP2	Suitable for wood & steel, quick-release chuck clamping range 1.5-13, without rechargeable battery

Accessories

Cordless drill/driver Type 71161164	070200 71161164
Battery starter set Type 92604323	073832 92604323
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18