


CNMG 120416, Grade: CA515

Order data

Order number	250373 CA515
GTIN	4960664675371
Item class	25E

Description

CNMG 120416 CA515 Grade: CA515

Chip breaker: PH

Cutting depth a_p : 1 - 10 mm

Feed f : 0.25 - 0.8 mm/rev.

Cutting speed v_c main application: 70 - 430 m/min

Technical description

Main application	P
Corner radius	1.6 mm
Cutting depth a_p	1 - 10 mm
Cutting conditions	continuous
Feed f	0.25 - 0.8 mm/rev.
Cutting speed v_c main application	70 - 430 m/min
Chip breaker	PH
Grade	CA515

Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	CNMG 120416
Number of changes/inserts	4
Type of product	Indexable insert for turning