

**Abrasive flap disc long life ZA, conical, Ø 115 mm, Grit: 60****Order data**

Order number	565284 60
GTIN	4062406159405
Item class	52M

Description**Version:**

- **High-quality zirconium aluminium oxide (ZA) for high abrasive performance.**
- **Glass fibre pad for optimum contact pressure.**
- **Suitable for both steel and stainless steel.**
- **Best results on angle grinders of all power classes.**

long life - very closely spaced flap strips, for **maximum tool life**.

Application:

General purpose abrasive disc operations, surface abrasion, material removal and edge smoothing.

Technical description

Bore Ø	22.23 mm
Disc Ø	115 mm
Shape description	dished
Grinding media	Zirconium abrasive (ZA)

Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		