



## Abrasive flap disc speed+ ZA, flat, Ø 125 mm, Grit: 40



### Order data

Order number	565299 40
GTIN	4062406159559
Item class	52M

### Description

#### Version:

- **High-quality zirconium aluminium oxide (ZA) for high abrasive performance.**
- **Glass fibre pad for optimum contact pressure.**
- **Suitable for both steel and stainless steel.**
- **Best results on angle grinders of all power classes.**

**speed+** - optimised flap strip arrangement, for effectiveness similar to a fibre disc with **highly aggressive characteristics.**

#### Application:

Edge smoothing, material removal.  
 maximum circumferential speed: 80 m/s  
 Shape description: flat  
 Bore Ø: 22.23 mm

### Technical description

Shape description	flat
Disc Ø	125 mm
Bore Ø	22.23 mm

Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		