

Mitutoyo
U-WAVE-TM transmitter for external micrometers, Type: IP67

Order data

Order number	498892 IP67
GTIN	4946368735627
Item class	44A

Description
Version:

Wireless data transmission system U-WAVE fit.

- **Direct connection of the transmitter to the rear of the measuring instrument - no annoying cables.**
- **Reliable data transfer confirmation by signal beep or red/orange/green LED signal.**
- **Range approx. 20 metres (in a line of sight)**
- **Outstanding battery life: 400,000 data transmissions using just one battery.**

Suitable for:

Coolant Proof IP65 external micrometers / dial indicators No. 434065, 434461, 434622

Note:

Please order the connection module and transmitter.

Technical description

Feedback	LED
Type of product	Transmitter

