


CCMT 120412, Grade: CA515

Order data

Order number	260206 CA515
GTIN	4960664674985
Item class	25E

Description

CCMT 120412 CA515 Grade: CA515

Chip breaker: GK

Tolerance: M

Cutting depth a_p : 0.5 - 3 mm

Feed f : 0.1 - 0.3 mm/rev.

Cutting speed v_c main application: 110 - 380 m/min

Technical description

Corner radius	1.2 mm
Cutting speed v_c main application	110 - 380 m/min
Cutting conditions	continuous
Cutting depth a_p	0.5 - 3 mm
Feed f	0.1 - 0.3 mm/rev.
Chip breaker	GK
Main application	P

Grade	CA515
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	CCMT 120412
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning