



Double wedge clamp, Thread M: M4



Order data

Order number	370010 M4
GTIN	4046368870509
Item class	37M

Description

Version:

- Aluminium profile with steel wedge including screws.
- Space-saving multiple clamping.

Application:

Particularly suitable for clamping round and flat parts.

Technical description

B ₁	10.4 mm
Thread M	M4
Height H ₂	5.6 mm
suitable for hex socket -AF	3 mm
B ₂	12.7 mm
Clamping force	2.2 kN
Maximum spreading tension	13.2 mm
H ₁	12.7 mm
maximum tightening torque	3.4 Nm
Length L	15.9 mm

Height H	14.5 mm
Width B	12.3 mm
Type of product	Wedge clamp