



Double wedge clamp, Thread M: M8



Order data

Order number	370010 M8
GTIN	4046368871001
Item class	37M

Description

Version:

- Aluminium profile with steel wedge including screws.
- Space-saving multiple clamping.

Application:

Particularly suitable for clamping round and flat parts.

Technical description

H ₁	25.4 mm
suitable for hex socket -AF	6 mm
Height H ₂	12.7 mm
B ₂	25.4 mm
Clamping force	8.9 kN
B ₁	20.8 mm
Thread M	M8
Maximum spreading tension	26.9 mm
maximum tightening torque	14.5 Nm
Length L	31.7 mm

Height H	25.9 mm
Width B	24.8 mm
Type of product	Wedge clamp