



Clamping mandrel for through hole, D1: 35,3mm



Order data

Order number	370015 35,3
GTIN	4046368382507
Item class	37M

Description

Version:

- Base body of structural steel including steel screw.
- 5-face machining possible.
- Very high repetition accuracy.
- Easy machining of the base body at the desired clamping \emptyset .

Application:

For clamping workpieces in an existing bore.

Technical description

$\emptyset D_3$	M 12
D_2 smallest clamping \emptyset	23 mm
H	31.8 mm
H_1	25.4 mm
External $\emptyset D_1$	35.3 mm
External $\emptyset D$	56 mm

Clamping force	26.3 kN
Ø D ₄	M 4/45.5
maximum tightening torque	150 Nm
max. clamping travel	0.38 mm
Tolerance external Ø	h9
Type of product	Mandrel