



## Double wedge clamp, Thread M: M6



### Order data

Order number	370010 M6
GTIN	4046368870752
Item class	37M

### Description

#### Version:

- Aluminium profile with steel wedge including screws.
- Space-saving multiple clamping.

#### Application:

Particularly suitable for clamping round and flat parts.

### Technical description

suitable for hex socket -AF	5 mm
B <sub>1</sub>	16.1 mm
Height H <sub>2</sub>	9.5 mm
Clamping force	6.7 kN
Thread M	M6
B <sub>2</sub>	19 mm
H <sub>1</sub>	19.05 mm
Maximum spreading tension	20.3 mm
maximum tightening torque	14.3 Nm
Length L	23.8 mm

Height H	19 mm
Width B	18.6 mm
Type of product	Wedge clamp