



Double wedge clamp, Thread M: M12



Order data

Order number	370010 M12
GTIN	4046368871506
Item class	37M

Description

Version:

- Aluminium profile with steel wedge including screws.
- Space-saving multiple clamping.

Application:

Particularly suitable for clamping round and flat parts.

Technical description

Clamping force	15.6 kN
B ₂	38.1 mm
B ₁	30.8 mm
Thread M	M12
Maximum spreading tension	39.9 mm
H ₁	38.1 mm
Height H ₂	19 mm
suitable for hex socket -AF	10 mm
maximum tightening torque	38.4 Nm
Length L	47.6 mm

Height H	38.6 mm
Width B	37.3 mm
Type of product	Wedge clamp