

**Adjustable spanner with quick adjustment, overall length: 200mm****Order data**

Order number	813920 200
GTIN	3662424092206
Item class	83H

**Description****Version:**

Ergonomic shape, chrome-plated. Jaw angle 22.5°. Quick time-saving adjustment mechanism. With metric and imperial **scales** on the jaws.

**Standard:**

**ISO 6787, DIN 3117, ASME B107.100**

**Technical description**

overall length	200 mm
overall length	8 in
maximum width across flats	33 mm
Standard	ISO 6787
Standard	DIN 3117
Standard	ASME B107.100
Jaw position	22.5 degrees
Surface	chrome-plated
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners

