



## Adjustable spanner with quick adjustment, overall length: 255mm



### Order data

Order number	813920 255
GTIN	3662424092213
Item class	83H

### Description

**Version:**

Ergonomic shape, chrome-plated. Jaw angle 22.5°. Quick time-saving adjustment mechanism. With metric and imperial **scales** on the jaws.

**Standard:**

**ISO 6787, DIN 3117, ASME B107.100**

### Technical description

overall length	10 in
overall length	255 mm
maximum width across flats	38 mm
Standard	ISO 6787
Standard	DIN 3117
Standard	ASME B107.100
Jaw position	22.5 degrees
Surface	chrome-plated
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners

