



Adjustable spanner with quick adjustment, overall length: 150mm



Order data

Order number	813920 150
GTIN	3662424092190
Item class	83H

Description

Version:

Ergonomic shape, chrome-plated. Jaw angle 22.5°. Quick time-saving adjustment mechanism. With metric and imperial **scales** on the jaws.

Standard:

ISO 6787, DIN 3117, ASME B107.100

Technical description

maximum width across flats	23 mm
overall length	6 in
overall length	150 mm
Standard	ISO 6787
Standard	DIN 3117
Standard	ASME B107.100
Jaw position	22.5 degrees
Surface	chrome-plated
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners

