



## Adjustable spanner with quick adjustment, overall length: 110mm



### Order data

Order number	813920 110
GTIN	3662424092183
Item class	83H

### Description

**Version:**

Ergonomic shape, chrome-plated. Jaw angle 22.5°. Quick time-saving adjustment mechanism. With metric and imperial **scales** on the jaws.

**Standard:**

**ISO 6787, DIN 3117, ASME B107.100**

### Technical description

overall length	4 in
maximum width across flats	17 mm
overall length	110 mm
Standard	ISO 6787
Standard	DIN 3117
Standard	ASME B107.100
Jaw position	22.5 degrees
Surface	chrome-plated
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners

