



Adjustable spanner with quick adjustment, overall length: 300mm



Order data

Order number	813920 300
GTIN	3662424092220
Item class	83H

Description

Version:

Ergonomic shape, chrome-plated. Jaw angle 22.5°. Quick time-saving adjustment mechanism. With metric and imperial **scales** on the jaws.

Standard:

ISO 6787, DIN 3117, ASME B107.100

Technical description

overall length	300 mm
maximum width across flats	41 mm
overall length	12 in
Standard	ISO 6787
Standard	DIN 3117
Standard	ASME B107.100
Jaw position	22.5 degrees
Surface	chrome-plated
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners

