

**Garant****Abrasive flap disc long life ZA, conical, Ø 115 mm, Grit: 120****Order data**

Order number	565264 120
GTIN	4062406162405
Item class	51M

**Description****Version:**

- Premium zirconium aluminium oxide (ZA) for maximum abrasive performance.
- Sturdy polyester cotton mixed fabric for ideal wear characteristics and stability, even when used on edges.
- Sturdy glass fibre pad for optimum contact pressure.
- Suitable for both steel and stainless steel.
- Best results on low-power and high-power angle grinders.

**long life** - very closely spaced flap strips, for **maximum tool life**.

**Application:**

General purpose abrasive disc operations, surface abrasion, material removal and edge smoothing.

**Technical description**

Bore Ø	22.23 mm
Grit	120
Disc Ø	115 mm

Shape description	dished
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		
dry	suitable		