

Garant

Abrasive flap disc speed ZA, flat, Ø 125 mm, Grit: 120



Order data

| | |
|--------------|---------------|
| Order number | 565275 120 |
| GTIN | 4062406162528 |
| Item class | 51M |

Description

Version:

- Premium zirconium aluminium oxide (ZA) for maximum abrasive performance.
- Sturdy polyester cotton mixed fabric for ideal wear characteristics and stability, even when used on edges.
- Sturdy glass fibre pad for optimum contact pressure.
- Suitable for both steel and stainless steel.
- Best results on low-power and high-power angle grinders.

speed - flat flap strip arrangement, for **high metal removal rate** and long tool life.

Application:

Precise chamfering, edge smoothing and surface abrasion.

Technical description

| | |
|-------------------|----------|
| Disc Ø | 125 mm |
| Grit | 120 |
| Shape description | flat |
| Bore Ø | 22.23 mm |

| | |
|---|-------------------------|
| Grinding media | Zirconium abrasive (ZA) |
| Grinding medium code | ZA |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 125 mm |
| optimised for material | INOX |
| optimised for material | Steel |
| maximum circumferential speed | 80 m/s |
| Type of product | Abrasive flap disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| Uni | suitable | | |
| dry | suitable | | |