

Garant**X-LOCK abrasive flap disc long life ZA, conical, Ø 125 mm, Grit: 80****Order data**

Order number	565279 80
GTIN	4062406162559
Item class	51M

Description**Version:**

- **Premium zirconium aluminium oxide (ZA) for maximum abrasive performance.**
- **Sturdy polyester cotton mixed fabric for ideal wear characteristics and stability, even when used on edges.**
- **Sturdy glass fibre pad for optimum contact pressure.**
- **Suitable for both steel and stainless steel.**
- **Best results on low-power and high-power angle grinders.**

long life - very closely spaced flap strips, for **maximum tool life**.

Quick disc change without using tools using the X-LOCK System.

Application:

General purpose abrasive disc operations, surface abrasion, material removal and edge smoothing.

Note:

X-LOCK abrasive flap discs are upwards-compatible and can also be used on conventional angle grinders.

Technical description

Grit	80
Shape description	dished
Disc Ø	125 mm
Bore Ø	22.23 mm
Series	X-LOCK system
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		
dry	suitable		