



Rough grinding disc Silver, Disc Ø×disc width: 178X7mm



Order data

Order number	560453 178X7
GTIN	4054596444041
Item class	53M

Description

Version:

Silver rough grinding disc with a proportion of **precision-shaped ceramic grit** for a high metal removal rate and long service life. For **stainless steel and steel**.

Application:

Suitable for material removal by abrasion and heavy-duty cutting.

Specification:

A36P-BF.

Technical description

Bore Ø	22.23 mm
Disc Ø	178 mm
Disc thickness	7 mm
Series	SILVER
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %

recommended approach angle	20-30 degrees
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Rough grinding wheel

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		