



## Rough grinding disc Silver, Disc Ø×disc width: 125X7mm



### Order data

Order number	560453 125X7
GTIN	4054596443884
Item class	53M

### Description

#### Version:

**Silver** rough grinding disc with a proportion of **precision-shaped ceramic grit** for a high metal removal rate and long service life. For **stainless steel and steel**.

#### Application:

Suitable for material removal by abrasion and heavy-duty cutting.

#### Specification:

**A36P-BF.**

### Technical description

Bore Ø	22.23 mm
Disc thickness	7 mm
Disc Ø	125 mm
Series	SILVER
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %

recommended approach angle	20-30 degrees
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Rough grinding wheel

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		