



Rough grinding disc Silver, Disc Ø×disc width: 230X7mm



Order data

Order number	560453 230X7
GTIN	4054596444140
Item class	53M

Description

Version:

Silver rough grinding disc with a proportion of **precision-shaped ceramic grit** for a high metal removal rate and long service life. For **stainless steel and steel**.

Application:

Suitable for material removal by abrasion and heavy-duty cutting.

Specification:

A36P-BF.

Technical description

Disc thickness	7 mm
Disc Ø	230 mm
Bore Ø	22.23 mm
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	20-30 degrees

optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Rough grinding wheel

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		