

Garant

Divider wall (2 columns and 3 perforated panels) single-sided, Width: 1000mm

**Order data**

Order number	955430 1000
GTIN	4062406163273
Item class	91P

Description**Version:**

Columns (steel tubes 60×40×2 mm) with level compensation and **insertion slots** at the **front** and **back** to hold storage shelves etc. Threaded sockets on the inside of the columns for fitting (screwing on) perforated panels No. 928070; 928071.

Perforated panels with □ 9×9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders.

Application:

As room dividers, for privacy and for viewable and versatile tool storage.

Colour:

Perforated panels RAL 7035 light grey, columns RAL 7016 anthracite, **powder-coated.**

Technical description

Weight	32 kg
Width	1000 mm
maximum bay load	200 kg

Height	2125 mm
Perforated panel version	single-sided
Depth	660 mm
Design version	Steel hollow section construction
Hoffmann perforated panel grid interval	9×9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Perforated panel stand