

Garant GRIDLINE

CNC workbench with drawer casing 24G + 30G, Worktop length: 2000mm**Order data**

| | |
|--------------|---------------|
| Order number | 970615 2000 |
| GTIN | 4062406163389 |
| Item class | 9GK |

Description**Version:**

Workbench in sturdy steel construction. Drawer casing 24G and 30G, can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. With bamboo worktop.

Load capacity of drawers of the 24G casing: 75 kg.

Drawer load capacity of the 30G casing: 200 kg.

Colour:

Body RAL 7035 light grey, drawers RAL 7016 anthracite **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

For storage of tools, a drawer inlay No. 970705 is required.

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

| | |
|--------------------------|--------|
| Weight | 270 kg |
| Drawer body right, width | 750 mm |
| Drawer body left, width | 600 mm |
| Height | 850 mm |
| Worktop thickness | 50 mm |
| Drawer usable depth | 600 mm |
| Drawer body height | 800 mm |

| | |
|---|--|
| Drawer usable depth in G | 24 |
| Drawer body depth | 700 mm |
| Worktop depth | 750 mm |
| Workbench/desk load capacity - maximum distributed load (on wood) | 1000 kg |
| Worktop length | 2000 mm |
| Drawers usable width (body on the right) | 650 mm |
| Drawers usable width (body on the left) | 500 mm |
| Drawers usable width in G (body on the left) | 20 |
| Drawers usable width in G (body on the right) | 26 |
| Material thickness | 1 mm |
| Workbench height | 850 mm |
| Insert thickness | 50 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Drawer runner extension | Anti-tilt lock |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | CNC workbench |

Accessories

| | |
|--|------------|
| Drawer with one-handed individual drawer release system, 200 kg Drawer front height 75 mm | 931168 75 |
| Drawer with one-handed individual drawer release system, 200 kg Drawer front height 100 mm | 931168 100 |
| Drawer, 75 kg Drawer front height 125 mm | 931043 125 |
| Drawer with one-handed individual drawer release system, 200 kg Drawer front height 300 mm | 931168 300 |
| Drawer, 75 kg Drawer front height 75 mm | 931043 75 |

| | |
|---|--------------|
| Lock plate for GridLine Type HU21 | 914227 HU21 |
| Drawer,75 kg Drawer front height 250 mm | 931043 250 |
| Drawer,75 kg Drawer front height 50 mm | 931043 50 |
| Drawer with one-handed individual drawer release system,200 kg Drawer front height 125 mm | 931168 125 |
| Drawer,75 kg Drawer front height 100 mm | 931043 100 |
| Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 2000 mm | 926001 2000 |
| Tool cabinet complete with drawers 200 kg Height mm / number of drawers 800/5 | 931115 800/5 |
| Tool cabinet complete with drawers 75 kg Height mm / number of drawers 800/6 | 931005 800/6 |