

Garant GRIDLINE

CNC workbench with drawer casing 30G, 26×24G, Worktop length: 1500mm**Order data**

Order number	970605 1500
GTIN	4062406163372
Item class	9GK

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer casing 30G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and **200 kg** load capacity. With bamboo worktop.

Colour:

Body RAL 7035 light grey, drawers RAL 7016 anthracite **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

For storage of tools, a drawer inlay No. 970705 is required.

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Worktop length	1500 mm
Support width	50 mm
Drawer body width	750 mm
Height	850 mm
Worktop depth	750 mm
Drawer usable depth	600 mm

Drawer body depth	700 mm
Worktop thickness	50 mm
Drawer usable width	650 mm
Drawer body height	800 mm
Weight	175 kg
Number of drawers	5
Drawer usable depth in G	24
Workbench/desk load capacity - maximum distributed load (on wood)	1000 kg
Drawer usable width in G	26
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	200 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	CNC workbench

Accessories

Drawer with one-handed individual drawer release system, 200 kg Drawer front height 125 mm	931168 125
Lock plate for GridLine Type HU21	914227 HU21
Drawer with one-handed individual drawer release system, 200 kg Drawer front height 300 mm	931168 300
	931168 75

Drawer with one-handed individual drawer release system,200 kg Drawer front height 75 mm

Drawer with one-handed individual drawer release system,200 kg Drawer front height 100 mm

931168 100

Stabilising plate Type 1

927122 1

Tool cabinet complete with drawers200 kg Height mm / number of drawers 800/5

931115 800/5

Support leg Height 800 mm

927000 800

Worktop thickness 50 mmof bamboo strips glued cross-wise Worktop length 1500 mm

926001 1500